


➔DOMETIC

RC 10.4G.70, RC 10.4P.70,  
RC 10.4G.90, RC 10.4P.90,  
RC 10.4P.9M, RC 10.4P.P  
RCS 10.5 (G/P/XG/XP)  
RCL 10.4 (EG/EP)  
RCD 10.5 (EG/EP/XEG/XEP)




⚠WARNING



⚠CAUTION




NOTICE



ON/OFF


1

ON




2

OFF




Settings

3



Cooling Capacity


4



Shelves


5

Out



6


In



Shelf Angle


7

RCD 10.5 (EG/EP/XEG/XEP)




## VG Fresh Base Out

8




## VG Fresh Base In

9




## Defrosting

10



## Storage


11



## Releasing Door

12


RCL 10.4EG / RCD 10.5 (G) / RCS 10.5 (G)  
RC 10.4G.70 / RC 10.4G.90




## Removing Frozen Compartment

13

RCL 10.4 (EG/EP)




RC 10.4P.70 / RC 10.4G.70 / RC 10.4P.90  
RC 10.4G.90 / RC 10.4P.9M / RC 10.4P.P / RCS 10.5 (G/P/XG/XP)



## Metal Clamps

14

RCL 10.4 (EG/EP)



**DOMETIC**