

GUIDE

NEW FOR OLD – SIMPLY SWAP

DOMETIC ABSORPTION AND COMPRESSOR FRIDGES

 **DOMETIC** **OUTDOOR**

CONTENTS

CRITERIA TO CONSIDER WHEN SWAPING THE “OLD” REFRIGERATOR

4-7

ABSORPTION FRIDGES

8-9

COMPRESSOR FRIDGES



DOMETIC ON THE WEB

Here's where you can find the complete Dometic range, with detailed information about all products. Plus, interesting facts about our company and download links for all of our catalogs.

dometic.com



NEW FOR OLD – SIMPLY SWAP

Would you like to replace your good old absorption refrigerator with a contemporary one of the Dometic 10, 8 or 5 series to enjoy more convenience, up-to-date technology and a real eye-catcher in your kitchen?

Our swap guide helps you to find out which absorption or compressor refrigerator model best suits your size requirements.



VENTILATION CLEARANCE

Please note that the unit dimensions given in the tables on the next pages refer to the size of the refrigerator only. The size and position of the ventilation openings may differ from those of your current fridge. For Dometic refrigerators, a clearance of 15 mm to 25 mm must be maintained to the vehicle wall in addition to the depth dimension of the unit.



HEIGHT COMPENSATION

If your new Dometic refrigerator is a bit smaller in height than its predecessor, you can easily compensate for the height difference by attaching feet to the unit. For Thetford models, a minimum distance of 12 mm to the floor must be maintained if no feet are attached to the appliance.

Besides these general notes, it is always advisable to read the installation instructions of the desired appliance before replacing a refrigerator.

ABSORPTION FRIDGES

↗DOMETIC MODEL RM 300 P/A / RM 301 / RM 4290L RM 4300 / RM 6291 / RM 7290L RM 7291L / RMS 850x	↗DOMETIC  <table><tr><td>Model</td><td>RMS 10.5T</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 548 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>76 L</td></tr><tr><td>SKU</td><td>9600027101</td></tr></table>	Model	RMS 10.5T	W x H x D (mm)	523 x 821 x 548 (+15 up to 25)	Technology	Absorption	Volume	76 L	SKU	9600027101	↗DOMETIC MODEL RM 855x / RMS 855x	↗DOMETIC  <table><tr><td>Model</td><td>RMS 10.5XT</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 603 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>90 L</td></tr><tr><td>SKU</td><td>9600027116</td></tr></table>	Model	RMS 10.5XT	W x H x D (mm)	523 x 821 x 603 (+15 up to 25)	Technology	Absorption	Volume	90 L	SKU	9600027116
Model	RMS 10.5T																						
W x H x D (mm)	523 x 821 x 548 (+15 up to 25)																						
Technology	Absorption																						
Volume	76 L																						
SKU	9600027101																						
Model	RMS 10.5XT																						
W x H x D (mm)	523 x 821 x 603 (+15 up to 25)																						
Technology	Absorption																						
Volume	90 L																						
SKU	9600027116																						
THETFORD MODEL N3090A / N3090E / N4090A N4100A / N4100E+ / N90 1P N90 2E / N3097A / N3097E N4097A / N4097E		THETFORD MODEL N3112A / N3112E / N4108A N4108E+ / N4112A / N112 1P N112 2E / N112 6E / N112 6A N3108E / N3108A / N97 1P N97 2E / N97 6E / N97 6A																					

↗DOMETIC MODEL RM 400R / RM 400 P/C / RM 415 RM 4400 / RM 4401LM / RM 4405LM RM 6401 / RM 7401 L / RM 7405L RM 850x	↗DOMETIC  <table><tr><td>Model</td><td>RM 10.5T</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 548 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>86 L</td></tr><tr><td>SKU</td><td>9600027098</td></tr></table>	Model	RM 10.5T	W x H x D (mm)	523 x 821 x 548 (+15 up to 25)	Technology	Absorption	Volume	86 L	SKU	9600027098	↗DOMETIC MODEL RML 8330 / RML 9330 / RML 9335 RML 9331 / RML 9430* / RML 9431* RML 9435*	↗DOMETIC  <table><tr><td>Model</td><td>RML 10.4(T)</td></tr><tr><td>W x H x D (mm)</td><td>420 x 1293 x 578 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>133 L</td></tr><tr><td>SKU</td><td>9600027272</td></tr></table>	Model	RML 10.4(T)	W x H x D (mm)	420 x 1293 x 578 (+15 up to 25)	Technology	Absorption	Volume	133 L	SKU	9600027272
Model	RM 10.5T																						
W x H x D (mm)	523 x 821 x 548 (+15 up to 25)																						
Technology	Absorption																						
Volume	86 L																						
SKU	9600027098																						
Model	RML 10.4(T)																						
W x H x D (mm)	420 x 1293 x 578 (+15 up to 25)																						
Technology	Absorption																						
Volume	133 L																						
SKU	9600027272																						
THETFORD MODEL N100 1P / N100 2E / N100 6E N100 6A / N3100A / N3104A N3100E / N3104A / N3104E N4100E+ / N4100A / N4104E+ N4104A / N104 1P / N104 2E N104 6E / N104 6A		*Replacement Kit needed (9600025974).																					

↔DOMETIC MODEL RM 4501 L / RM 4505 L / RM 7501 L RM 7505 L / RM 7601 L / RM 7605 L RMD 8501 / RMD 8505	↔DOMETIC  <table><tr><td>Model</td><td>RMD 10.5(T)</td></tr><tr><td>W x H x D (mm)</td><td>523 x 1245 x 550 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>153 L</td></tr><tr><td>SKU</td><td>9600014843</td></tr></table>	Model	RMD 10.5(T)	W x H x D (mm)	523 x 1245 x 550 (+15 up to 25)	Technology	Absorption	Volume	153 L	SKU	9600014843
Model	RMD 10.5(T)										
W x H x D (mm)	523 x 1245 x 550 (+15 up to 25)										
Technology	Absorption										
Volume	153 L										
SKU	9600014843										
THETFORD MODEL N3145A / N3145E+ / N3150A N3150E / N4145E+ N4145A N4150E+ / N150 6E / N150 6A N145 6E / N145 6A											
↔DOMETIC MODEL RM 7801 L RM 7805 L / RM 7851 L+ / RM 7855 L RMD 8551 / RMD 8555 / RML 8550 RML 8551 / RML 8555	↔DOMETIC  <table><tr><td>Model</td><td>RMD 10.5X(T)</td></tr><tr><td>W x H x D (mm)</td><td>523 x 1245 x 605 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>177 L</td></tr><tr><td>SKU</td><td>9600027265</td></tr></table>	Model	RMD 10.5X(T)	W x H x D (mm)	523 x 1245 x 605 (+15 up to 25)	Technology	Absorption	Volume	177 L	SKU	9600027265
Model	RMD 10.5X(T)										
W x H x D (mm)	523 x 1245 x 605 (+15 up to 25)										
Technology	Absorption										
Volume	177 L										
SKU	9600027265										
THETFORD MODEL N4175E+ / / N4170E+ / N4170A N4175A / N3170E / N3170A N3175A / N3175E / N175 6E N175 6A											
↔DOMETIC MODEL RM 200 / RM 2210 / RM 4200 RM 4210 / RM 4211 LM	↔DOMETIC  <table><tr><td>Model</td><td>RM 5310</td></tr><tr><td>W x H x D (mm)</td><td>486 x 618 x 474</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>60 L</td></tr><tr><td>SKU</td><td>9105703857 9105704417 (UK)</td></tr></table>	Model	RM 5310	W x H x D (mm)	486 x 618 x 474	Technology	Absorption	Volume	60 L	SKU	9105703857 9105704417 (UK)
Model	RM 5310										
W x H x D (mm)	486 x 618 x 474										
Technology	Absorption										
Volume	60 L										
SKU	9105703857 9105704417 (UK)										
↔DOMETIC MODEL RM 270 / RM 2251 / RM 4230L	↔DOMETIC  <table><tr><td>Model</td><td>RM 5330</td></tr><tr><td>W x H x D (mm)</td><td>486 x 821 x 474</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>70 L</td></tr><tr><td>SKU</td><td>9105703862 9105704418 (UK)</td></tr></table>	Model	RM 5330	W x H x D (mm)	486 x 821 x 474	Technology	Absorption	Volume	70 L	SKU	9105703862 9105704418 (UK)
Model	RM 5330										
W x H x D (mm)	486 x 821 x 474										
Technology	Absorption										
Volume	70 L										
SKU	9105703862 9105704418 (UK)										

ABSORPTION FRIDGES

↔DOMETIC MODEL RM 275 / RM 4281 LM / RM 4261	↔DOMETIC  <table><tr><td>Model</td><td>RM 5380</td></tr><tr><td>W x H x D (mm)</td><td>486 x 821 x 474</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>80 L</td></tr><tr><td>SKU</td><td>9105703865</td></tr></table>	Model	RM 5380	W x H x D (mm)	486 x 821 x 474	Technology	Absorption	Volume	80 L	SKU	9105703865
Model	RM 5380										
W x H x D (mm)	486 x 821 x 474										
Technology	Absorption										
Volume	80 L										
SKU	9105703865										
↔DOMETIC MODEL RM 2254 / RM 4360 L / RM 7360 L	↔DOMETIC  <table><tr><td>Model</td><td>RM 8400</td></tr><tr><td>W x H x D (mm)</td><td>486 x 821 x 569</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>90 L</td></tr><tr><td>SKU</td><td>9500001550 Right door 9500001551 Left door</td></tr></table>	Model	RM 8400	W x H x D (mm)	486 x 821 x 569	Technology	Absorption	Volume	90 L	SKU	9500001550 Right door 9500001551 Left door
Model	RM 8400										
W x H x D (mm)	486 x 821 x 569										
Technology	Absorption										
Volume	90 L										
SKU	9500001550 Right door 9500001551 Left door										
↔DOMETIC MODEL RM 2253 / RM 4361 LM / RM 4365 LM RM 6361 L / RM 7361 L / RM 7365 L	↔DOMETIC  <table><tr><td>Model</td><td>RM 8401</td></tr><tr><td>W x H x D (mm)</td><td>486 x 821 x 569</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>90 L</td></tr><tr><td>SKU</td><td>9500001554 Right door 9500001555 Left Door</td></tr></table>	Model	RM 8401	W x H x D (mm)	486 x 821 x 569	Technology	Absorption	Volume	90 L	SKU	9500001554 Right door 9500001555 Left Door
Model	RM 8401										
W x H x D (mm)	486 x 821 x 569										
Technology	Absorption										
Volume	90 L										
SKU	9500001554 Right door 9500001555 Left Door										
↔DOMETIC MODEL RM 4270 / RM 6270 / RM 7270 L	↔DOMETIC  <table><tr><td>Model</td><td>RMS 8400</td></tr><tr><td>W x H x D (mm)</td><td>486 x 821 x 569</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>80 L</td></tr><tr><td>SKU</td><td>9500001579 Right door 9500001580 Left Door</td></tr></table>	Model	RMS 8400	W x H x D (mm)	486 x 821 x 569	Technology	Absorption	Volume	80 L	SKU	9500001579 Right door 9500001580 Left Door
Model	RMS 8400										
W x H x D (mm)	486 x 821 x 569										
Technology	Absorption										
Volume	80 L										
SKU	9500001579 Right door 9500001580 Left Door										

DOMETIC	
MODEL	
RM 6271 / RM 7271 L	
THETFORD	
MODEL	
N80 1P / N80 2E / N3080 / N4080E+	

DOMETIC	
	
Model	RMS 8401
W x H x D (mm)	486 x 821 x 569 (+15 up to 25)
Technology	Absorption
Volume	80 L
SKU	9105705370 Right door 9105705371 Left Door





ABSORPTION ADVANTAGE

NOISELESS COOLING WITH THREE ENERGY SOURCES

Absorption refrigerators run in silence, making them perfect for combined sleeping and cooking spaces. Plus, you can power them with mains, battery, and even LPG camping gas for flexible, reliable, virtually maintenance-free operation.

WHEN AN ABSORPTION REFRIGERATOR IS REPLACED WITH A COMPRESSOR UNIT, THE EXTERNAL VENTILATION GRIDS HAVE TO BE CLOSED.



COMPRESSOR FRIDGES

↗ DOMETIC MODEL RM 4501 L / RM 4505 L / RM 7501 L RM 7505 L / RM 7601 L / RM 7605 L RMD 8501 / RMD 8505	↗ DOMETIC  <table><tr><td>Model</td><td>RCD 10.5(T)</td></tr><tr><td>W x H x D (mm)</td><td>523 x 1282 x 535* (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>147 L</td></tr><tr><td>SKU</td><td>9600027684</td></tr></table>	Model	RCD 10.5(T)	W x H x D (mm)	523 x 1282 x 535* (+15 up to 25)	Technology	Compressor	Volume	147 L	SKU	9600027684
Model	RCD 10.5(T)										
W x H x D (mm)	523 x 1282 x 535* (+15 up to 25)										
Technology	Compressor										
Volume	147 L										
SKU	9600027684										
THETFORD MODEL N3145A / N3145E+ / N3150A N3150E / N4145E+ N4145A N4150E+ / N150 6E / N150 6A N145 6E / N145 6A / T2160											

↗ DOMETIC MODEL RM 7801 L / RM 7805 L / RM 7851 L+ RM 7855 L / RMD 8551 / RMD 8555 RML 8550 / RML 8551 / RML 8555	↗ DOMETIC  <table><tr><td>Model</td><td>RCD 10.5X(T)</td></tr><tr><td>W x H x D (mm)</td><td>523 x 1282 x 605* (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>177 L</td></tr><tr><td>SKU</td><td>9600028301</td></tr></table>	Model	RCD 10.5X(T)	W x H x D (mm)	523 x 1282 x 605* (+15 up to 25)	Technology	Compressor	Volume	177 L	SKU	9600028301
Model	RCD 10.5X(T)										
W x H x D (mm)	523 x 1282 x 605* (+15 up to 25)										
Technology	Compressor										
Volume	177 L										
SKU	9600028301										
THETFORD MODEL N4145E / N4145A / N4150E+ N4175E+ / N4150A / N4170E+ N4170A / N4175A / T2175											

↗ DOMETIC MODEL RML 8330 / RML 9330 / RML 9331 RML 9335 / RML 9430* / RML 9431* RML 9435*	↗ DOMETIC  <table><tr><td>Model</td><td>RCL 10.4ET</td></tr><tr><td>W x H x D (mm)</td><td>420 x 1293 x 595 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>151 L</td></tr><tr><td>SKU</td><td>9600049607</td></tr></table>	Model	RCL 10.4ET	W x H x D (mm)	420 x 1293 x 595 (+15 up to 25)	Technology	Compressor	Volume	151 L	SKU	9600049607
Model	RCL 10.4ET										
W x H x D (mm)	420 x 1293 x 595 (+15 up to 25)										
Technology	Compressor										
Volume	151 L										
SKU	9600049607										
↗ DOMETIC MODEL RML 8330 / RML 9330 / RML 9331 RML 9335 / RML 9430* / RML 9431* RML 9435*											

↗ DOMETIC MODEL RML 8330 / RML 9330 / RML 9331 RML 9335 / RML 9430* / RML 9431* RML 9435*	↗ DOMETIC  <table><tr><td>Model</td><td>RCL 10.4T</td></tr><tr><td>W x H x D (mm)</td><td>420 x 1293 x 595 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>128 L</td></tr><tr><td>SKU</td><td>9600027685</td></tr></table>	Model	RCL 10.4T	W x H x D (mm)	420 x 1293 x 595 (+15 up to 25)	Technology	Compressor	Volume	128 L	SKU	9600027685
Model	RCL 10.4T										
W x H x D (mm)	420 x 1293 x 595 (+15 up to 25)										
Technology	Compressor										
Volume	128 L										
SKU	9600027685										
↗ DOMETIC MODEL RML 8330 / RML 9330 / RML 9331 RML 9335 / RML 9430* / RML 9431* RML 9435*											

*Replacement Kit needed (9600025974).

*Replacement Kit needed (9600025974).

*Due to the internal ventilation system, the RCD is 37 mm taller than the listed predecessor models.
If required the ventilation can be removed and replaced with ventilation slots in the furniture.

↗DOMETIC MODEL - THETFORD MODEL -	↗DOMETIC  ModelRC 10.4T 70 W x H x D (mm)420 x 821 x 450 (+15 up to 25) TechnologyCompressor Volume70 L SKU9600028399	↗DOMETIC MODEL - THETFORD MODEL T1090 Floor level / T1090 Eye level T2090 Floor level / T2090 Eye level	↗DOMETIC  ModelRC 10.4T 90 W x H x D (mm)420 x 975 x 485 (+15 up to 25) TechnologyCompressor Volume90 L SKU9600028400
↗DOMETIC MODEL RM 300 P/A / RM 301 / RM 400 P/C RM 400R / RM 415 / RM 4290L / RM 4300 RM 4400 / RM 4401LM / RM 4405LM RM 6291 / RM 6401 / RM 7290L RM 7291L / RM 7401 L / RM 7405L RMS 850x / RM 850x THETFORD MODEL N3090A / N3090E / N4090A / N4100A- N4100E+ / N90 1P / N90 2E / N3097A N3097E / N4097A / N4097E / N100 1P N100 2E / N100 6E / N100 6A / N3100A- N3104A / N3100E / N3104A / N3104E N4100E+ / N4100A / N4104E+ N4104A / N104 1P / N104 2E N104 6E / N104 6A	↗DOMETIC  ModelRCS 10.5T W x H x D (mm)532 x 821 x 555 (+15 up to 25) TechnologyCompressor Volume83 L SKU9600028196	↗DOMETIC MODEL RM 855x / RMS 855x THETFORD MODEL N3112A / N3112E / N4108A N4108E+ / N4112A / N112 1P N112 2E / N112 6E / N112 6A N3108E / N3108A / N97 1P N97 2E / N97 6E / N97 6A	↗DOMETIC  ModelRCS 10.5XT W x H x D (mm)523 x 821 x 610 (+15 up to 25) TechnologyCompressor Volume98 L SKU9600028199



Dometic is a global company that makes mobile living easy – by providing great solutions to satisfy people's essential needs when they are on the move. Like cooking, taking care of personal hygiene and maintaining a pleasant temperature. We offer smart and reliable products with outstanding design.





THE FULL RANGE

View Products:

dometic.com

UNITED KINGDOM
DOMETIC UK LTD.

Dometic House, The Brewery,
Blandford St. Mary
Dorset DT11 9LS

Tel 0344 626 0133

Fax 0344 626 0143

Mail sales@dometic.co.uk

Net dometic.com

GERMANY
DOMETIC GERMANY GMBH

Hollefeldstraße 63
D-48282 Emsdetten

Tel +49 (0) 2572 879-0

Mail info@dometic.de

Net dometic.com

